



AIRsteril®

MULTIFLEX RANGE

BREATH FRESH AIR

PRODUCTS: MF20 // MF40 // MF60 // MF80



PURIFI
TECHNOLOGY

T: 045 250 092
E: sales@purifair.ie
W: www.purifair.ie



LIFTS HYGIENE STANDARDS TO A LEVEL IMPOSSIBLE WITH TRADITIONAL CLEANING ALONE

REMOVE ODOURS, CONTROL INFECTION & IMPROVE HYGIENE

- Reduces harmful viruses
- Circulates fresh clean air
- Breaks down unwanted bacteria
- Attacks odours at their source
- Removes unhealthy microbes from the air
- Makes every room smell freshly cleaned
- Maintains sanitized surfaces
- Stops mould and fungi growth
- Clears smelly compounds in the air 24/7



› HYGIENE PROBLEMS

In enclosed spaces, lingering unpleasant odours are an embarrassing problem. Airborne microorganisms create offensive odours, spread infections and compromise hygiene standards, bacteria breed so quickly they cannot be cleared with traditional cleaning. Masking odours can create a more unpleasant environment.

The Multiflex range is completely safe for use in areas of continuous occupation.

› PERFECT FOR USE IN

- › Changing rooms - gymnasiums, offices
- › Kitchens and food preparation areas
- › Care homes - lounges, corridors, receptions
- › Waiting rooms
- › Open plan offices
- › Nurseries

Area Size	20m ²	40m ²	60m ²	80m ²
Odour & infection control	MF20	MF40	MF60	MF80

- › Fan operation distributes cleaning air
- › Annual lamp change maintains performance
- › Robust vandal resistant Aluminium casing
- › Wall or ceiling mountable on four screws
- › Plug in or quickly wired into fused spur



THE MOST ADVANCED BACTERIA CONTROL TECHNOLOGY OF ITS KIND, USED BY THE BEST PROFESSIONALS IN THE BUSINESS



› SERVICING MADE EASY

Power must be disconnected before attempting any servicing and only undertaken by a competent individual. All AIRsteril partners have fully trained engineers to carry out all servicing work.

The MF cover is easily removed by taking out four screws, then the two finger screws removed from the lamp housing plate allow lamp replacement. Any dust or debris build up should be cleared from the fan and interior.

Lamps must be changed on an annual basis to maintain performance.

› HOW OUR AIR SILENT SYSTEM WORKS

All AIRsteril units utilise our unique combination of 5 technologies. They eliminate unpleasant odours and control harmful bacteria and viruses 24 hours a day, 365 days of the year.

The MF units are suitable for use in areas of continuous occupation in enclosed spaces. The number in the unit code signifies the floor area - an MF40 covers 40m² and an MF80 covers 80m². For larger areas a combination of MF units is used, for infection control only a lower powered unit can be used. The MF is fan driven and can easily be ceiling or wall mounted for continuous operation via a fused spur, or plugged in. Alternatively, it is supplied with rubber feet and can be placed on a high surface.

TECHNICAL DETAILS

Multiflex Unit Dimensions

430mm(l)x 130mm(w)x 100mm(d)

Power Supply

220-230V 33 watts

Set Up

Wall or ceiling mounting. Easy marking and fixing at four points.

Construction

Anodised aluminium extrusion.

Weight

2.4kg

Operation

Continuous, indicated by blue lamp. Requires annual lamp change.